



31000v2 DAPI/Hoechst/AMCA




EX: $350\text{nm} \pm 50\text{nm}$, DM: 400nm long pass, EM: $460\text{nm} \pm 50\text{nm}$

41017 Endow GFP/EGFP Bandpass




EX: 470nm \pm 40nm, DM: 495nm long pass, EM: 525nm \pm 50 nm

41028 EYFP/Venus/Citrine/Topaz Bandpass




EX: 500nm \pm 20nm, DM: 515nm long pass, EM: 535nm \pm 30 nm

41007a Cy3™ (With narrow band excitation filter)




EX: 545nm \pm 30nm, DM: 570nm long pass, EM: 610nm \pm 75 nm

41004 Texas Red®



EX: 560nm \pm 55nm, DM: 595nm long pass, EM: 647nm \pm 75 nm

41008 Cy5™



EX: 620nm \pm 60nm, DM: 660nm long pass, EM: 700nm \pm 75 nm